

# LSRII Filter Configuration

Blue				
Detector A 780/60	Detector B 695/40	Detector D 610/20	Detector E 575/25	Detector F 530/30
PE Cy7	PerCP	PE-Texas Red	PE	GFP
	PerCP-Cy5.5	Alexa Fluor 610	PI	Alexa Fluor 488
	PE-Cy5			FITC
				CFSE

Red		
Detector A 780/60	Detector B 710/50	Detector C 660/20
APC-Cy7	Alexa Fluor 700	APC
APC-H7		Alexa Fluor 647
APC-efluor 780		Alexa Fluor 633
		Cy5

Ultra-Violet	
Detector A 530/30	Detector B 450/50
Hoescht Red	Alexa Fluor 350
	Live/Dead Fix Blue
	DAPI
	Hoescht Blue

Violet			
Detector A 710/50	Detector B 650/50	Detector C 525/50	Detector D 450/50
BV711	BV650	V500	Pacific Blue
Qdot 705	Qdot 655	BV510	BV421
		AmCyan	efluor 450
		Qdot 525	V450